
# Endevco®

## Piezoelectric accelerometer

### Model 2272



The Endevco® model 2272 is a piezoelectric accelerometer designed specifically for vibration measurement at temperature extremes. The unit is hermetically sealed for use in harsh environments and features long term stability. Its unique sensing elements offer an unusually flat temperature response over a broad range. The accelerometer is a self-generating device that requires no external power source for operation.

The model 2272 operates in compression mode and exhibits excellent output sensitivity stability over time. Signal ground is connected to the outer case of the unit. When used with an isolated mounting stud, the accelerometer is electrically isolated from ground. The accelerometer features a 10-32 UNF-2A side-connector. A low-noise coaxial cable is supplied for error-free operation.

Endevco signal conditioner models 133, 2775B, 2771C, 6634C or Oasis 2000 computer-controlled 4990A-X system are recommended for use with this high impedance accelerometer with cards 428 and/or 433.

**ENDEVCO** www.endevco.com Tel: +1 (866) ENDEVCO [+1 (866) 363-3826]

Piezoelectric accelerometers | Piezoresistive accelerometers | IEPE accelerometers | Variable capacitance accelerometers | Piezoresistive pressure sensors | Piezoelectric pressure sensors | High intensity microphones | Inertial sensors | Signal conditioners and supportive instrumentation | Cable assemblies

### Piezoelectric accelerometer

Model 2272

### **Specifications**

The following performance specifications conform to ISA-RP-37.2 (1964) and are typical values, referenced at +75°F (+24°C) and 100 Hz, unless otherwise noted. Calibration data, traceable to National Institute of Standards and Technology (NIST), is supplied.

Dynamic characteristics	Units	Value
Charge sensitivity		
Typical	pC/g	13
Minimum	pC/g	10.4
Frequency response		See typical amplitude response
Resonance frequency, typical	kHz	30
Minimum	kHz	28
Amplitude response [1]		
±5%	Hz	1 to 5000
±1dB (ref.)	Hz	1 to 9000
Temperature response [3]		See typical curve
Transverse sensitivity	%	≤ 3
Amplitude linearity		
Per 1000 g, 0 to 2000 g	%	1
Electrical characteristics		
Output polarity		Acceleration directed into the base of the unit produces positive output
Resistance	GΩ	$\geq 10$
at +500°F (+260°C)	MΩ	≥ 100
Capacitance	pF	2700
Grounding	pi	Signal ground connected to case
Environmental characteristics		
Temperature range		-452°F to +500°F (-269°C to +260°C)
Humidity		Hermetically sealed
Sinusoidal vibration	g pk	1000
Shock limit [2]	g pk	2000
Base strain sensitivity	equiv. g pk/µ strain	0.04
Thermal transient sensitivity	equiv.g pk/°F (/°C)	0.08 (0.144)
Electromagnetic sensitivity	equiv. g rms/gauss	0.0002
Acoustic sensitivity at 140 dB SPL	equiv. g	0.001
at 170 dB SPL	equiv. g	0.03
Pressure		
Low frequency up to 1000 Hz	equiv. g/psi	0.01
Salt spray		Will meet MIL-E-5272 with potted connector
Physical characteristics		
Dimensions		See outline drawing
Weight	oz (gm)	0.95 (27)
Case material		Stainless steel
Connector		10-32 UNF-2A Thd, mates with Endevco 3000 series cable
Mounting torgue	lbf-in (Nm)	18 (2)
······		
Calibration		
Supplied:	- 0/-	
Charge sensitivity	pC/g	
Capacitance Maximum transverse consitivity	pF	
Maximum transverse sensitivity	%	20 Hz to 5000 Hz
Charge frequency response	%	
	dB	5000 Hz thru resonance

**ENDEVCO** www.endevco.com Tel: +1 (866) ENDEVCO [+1 (866) 363-3826]

# Endevco®

## Piezoelectric accelerometer

Model 2272

#### Accessories

Product	Description	
2981-12	Mounting stud, 10-32, Hex I.D.	Included
3090C-120	Cable assembly, 10 ft	Included
EHM464	Hex key wrench	Included
2981-3	Mounting stud 10-32 adapter	Optional
133	Signal conditioner	Optional
2771C	In-line charge converter IEPE powered	Optional
2775B	Signal conditioner	Optional
6634C	Signal conditioner	Optional
4990A-X	OASIS 2000 computer-controlled system with 428 and/or 433	Optional
CS330	Calibration cryogenic temerature response	Optional

### Contact

#### ENDEVCO

www.endevco.com Tel: +1 (866) ENDEVCO [+1 (866) 363-3826]

#### Notes:

- 1. Low-end response of the transducer is a function of its associated electronics.
- 2. Short duration shock pulses, such as those generated by metal-to-metal impacts, may excite transducer resonance and cause linearity errors. Request the TP290 for more details.
- 3. Exposure to rapid temperature changes greater than 100°F (38°C) per minute may cause the device to produce spurious high frequency discharges for several minutes.
- 4. Maintain high levels of precision and accuracy using Endevco's factory calibration services. Call Endevco's inside sales force at 866-ENDEVCO for recommended intervals, pricing and turn-around time for these services as well as for quotations on our standard products.



Continued product improvement necessitates that Endevco reserve the right to modify these specifications without notice. Endevco maintains a program of constant surveillance over all products to ensure a high level of reliability. This program includes attention to reliability factors during product design, the support of stringent Quality Control requirements, and compulsory corrective action procedures. These measures, together with conservative specifications have made the name Endevco synonymous with reliability. 082019